



Air conditioners

Heating & Cooling

Siesta

Wall mounted unit

- » Indoor unit silent operation
- » Vertical auto swing
- » Standard air filter
- » SEER : A
- » Gold fin anti corrosion treatment on outdoor heat exchanger



www.daikin.eu



ATXN-L

Heating & Cooling

Siesta

INDOOR UNIT			ATXN25L	ATXN35L	ATXN50L	
Cooling capacity	Min./Nom./Max.	kW	1.30/2.52/3.00	1.30/3.32/3.80	1.88/5.45/6.20	
Heating capacity	Min./Nom./Max.	kW	1.30/2.84/4.00	1.30/3.50/4.80	1.32/5.62/6.60	
Seasonal efficiency (according to EN14825)	Cooling	Energy label	A			
		Pdesign	kW	2.52	3.32	5.45
		SEER		5.29	5.48	5.50
	Heating (Average climate)	Annual energy consumption	kWh	167	213	347
		Energy label		A		
		Pdesign	kW	1.91	2.35	4.40
Nominal efficiency (cooling at 35°/27° nominal load, heating at 7°/20° nominal load)	SCOP		3.62	3.81	3.46	
	Annual energy consumption	kWh	740	864	1,780	
	EER		3.41	3.24	3.55	
	COP		4.06	3.76	3.75	
	Annual energy consumption	kWh	370	513	768	
Energy label	Cooling		A			
	Heating		A			
Casing	Colour		White			
Dimensions	Unit	HeightxWidthxDepth	288x800x212		310x1,065x229	
Weight	Unit		9		14	
Fan - Air flow rate	Cooling	Super high/High/Nom./Low/Silent operation	m ³ /min	10.68/9.78/9.47/6.06/4.68	11.10/10.14/9.85/6.54/4.68	
	Heating	Super high/High/Nom./Low/Silent operation	m ³ /min	10.68/9.78/7.68/6.06/4.68	11.10/10.14/7.98/6.54/4.68	
Sound power level	Cooling	Nom.	dBA	53	54	
Sound pressure level	Cooling	Super high/High/Nom./Low/Silent operation	dBA	41/40/34/29/24	42/41/34/30/25	
	Heating	High/Nom./Low/Silent operation	dBA	40/34/29/24	41/34/30/25	
Piping connections	Liquid	OD	mm	6.35		
	Gas	OD	mm	9.52		
	Drain	OD	mm	12.70		
Power supply	Phase / Frequency / Voltage	Hz / V	1~ / 50 / 220-240			

(1) EER/COP according to Eurovent 2012.

OUTDOOR UNIT				ARXN25L	ARXN35L	ARXN50L
Dimensions	Unit	HeightxWidthxDepth	mm	550x658x289		753x855x328
Weight	Unit		kg	28	30	49
Sound power level	Cooling	Nom.	dBA	60	62	65
Sound pressure level	Cooling	High	dBA	46	48	51
Compressor	Type	Hermetic swing				
Operation range	Cooling	Ambient	Min.~Max.	°CDB 10~46		-10~46
	Heating	Ambient	Min.~Max.	°CWB -15~18		
Refrigerant	Type	R-410A				
	GWP	1,975				
Piping connections	Liquid	OD	mm	6.35		
	Gas	OD	mm	9.52		
	Drain	OD	mm	16.5		
Level difference	IU - OU	Max.	m	-		
Power supply	Phase / Frequency / Voltage	Hz / V	1~ / 50 / 220-240			



ATXN-L



REMOTE CONTROL



ARXN-L



Daikin's unique position as a manufacturer of air conditioning equipment, compressors and refrigerants has led to its close involvement in environmental issues. For several years Daikin has had the intention to become a leader in the provision of products that have limited impact on the environment. This challenge demands the eco design and development of a wide range of products and an energy management system, resulting in energy conservation and a reduction of waste.



Daikin Europe N.V. participates in the Eurovent Certification programme for Air conditioners (AC), Liquid Chilling Packages (LCP) and Fan coil units (FCU). Check ongoing validity of certificate online: www.eurovent-certification.com or using: www.certiflash.com

The present leaflet is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this leaflet to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this leaflet. All content is copyrighted by Daikin Europe N.V.

